

Puristusmittataulukko

IMM 1-, 2-, 3- ja 4 vahvisteiset

Päivitetty 5.2.2025


Letkutyyppi	Koko	03	04	05	06	08	10	12	16	20	24	32
	Tuumaa	3/16"	1/4"	5/16"	3/8"	1/2"	5/8"	3/4"	1"	1 1/4"	1 1/2"	2"

	SPT1**SN Holkki 1C/3P4010 Ei kuorita	1C-03	1C-04	1C-05	1C-06	1C-08	1C-10	1C-12	1C-16	3P-20	3P-24	3P-32
		14,0	15,0	17,2	20,0	22,6	26,5	30,3	38,0	45,8	54,0	67,4

	2SPT**SN Holkki 3P4010 Ei kuorita	3P-03	3P-04	3P-05	3P-06	3P-08	3P-10	3P-12	3P-16	3P-20	3P-24	3P-32
		16,1	16,9	18,8	20,5	24,4	27,9	32,1	39,6	48,6	56,4	69,5

	1**C Holkki 1C4010 Ei kuorita		1C-04	1C-05	1C-06	1C-08	1C-10	1C-12	1C-16			
			15,1	16,9	19,4	22,1	26,0	29,8	37,4			

	SPT2**C(H) Holkki 1C4010 Ei kuorita		1C-04	1C-05	1C-06	1C-08	1C-10	1C-12	1C-16			
			15,4	17,7	20,3	22,9	26,7	30,6	38,5			
	Holkki 3P4010		3P-04	3P-05	3P-06	3P-08	3P-10	3P-12	3P-16			
			16,4	18,3	20,1	23,5	27,0	31,2	39,6			

	SPT3**CH Holkki 3P4010 Ei kuorita				3P-06	3P-08	3P-10	3P-12	3P-16			
					20,9	25,1	28,7	32,6	40,5			

	SPT3**CT Holkki 2P4010				2P-06	2P-08	2P-10	2P-12	2P-16			
					22,0	26,2	29,2	34,1	42,3			
	Kuorittava				24	28	27	34	48			

	R12 Holkki 9P4010				9P-06	9P-08	9P-10	9P-12	9P-16	9P-20-R12	9P-24	9P-32
					22,6	27,0	30,6	33,2	41,7	50,1	59,0	70,5
	Kuorittava				26	28	31	34	48	54	62	64

	4SP Holkki 9P4010		9P-04		9P-06	9P-08	9P-10	9P-12	9P-16	9P-20	9P-24	9P-32
			17,5		22,6	26,5	30,1	33,8	42,3	51,2	60,3	73,2
	Kuorittava		19		21	22,5	31	34	48	54	62	64

	4SH Holkki 9P4010							9P-12	9P-16	9P-20	9P-24	9P-32
								33,8	42,0	48,5	57,8	70,5
	Kuorittava							31	48			

HOLKIN
TYYPPI

PURISTUS-
MITTA

KUORINTAPITUUS

Letku ko ko	Supistuma mm	Letku ko ko	Supistuma mm	Letku ko ko	Supistuma mm
1/4"	0,2-0,6	5/8"	0,3-0,7	1 1/4"	0,4-1,2
3/8"	0,2-0,6	3/4"	0,4-0,6	1 1/2"	0,4-1,4
1/2"	0,3-0,7	1"	0,4-0,8	2"	0,4-1,4

Arvot ovat ohjeellisia. Virheettömän tuloksen takaamiseksi on syytä mitata liittimen reiän supistuma tulkkisarjan avulla.